



Watertight Series, Locking Receptacle, 15A 250VAC, 2-Pole 3-Wire Grounding, NEMA L6-15R, Yellow

By Bryant
Catalog # [BRY65W49](#)

Watertight Series, Locking Receptacle, 15A 250VAC, 2-Pole 3-Wire Grounding, NEMA L6-15R, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

Performance

Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes), UV resistance:All exposed materials are UV stabilized, Flammability:UL94V0 (boxes, covers, and plates)

Specifications

Industry Standard(s)	• IP69K in use • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	L6-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG
Number Of Poles	2-Pole



Current

Current/Amperage Rating	15 Amp
Description	
Amperage Rating	15 A
Voltage Rating Description	250 V
Voltage Rating	250 V

Dimensions

Width	3.10 in
Height	2.83 in
Length	4.56 in
Dimensions	4.56 in x 3.10 in x 2.83 in

General

Item Type	15A Watertight Single Receptacle
Type	Receptacle
UPC	781786379190
Color	Yellow

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)