



Watertight Series, Locking Receptacle, 20A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-20R, Yellow

By Bryant
Catalog # [BRY67W49](#)

Watertight Series, Locking Receptacle, 20A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-20R, Yellow

Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

Performance

Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes), UV resistance:All exposed materials are UV stabilized, Flammability:UL94V0 (boxes, covers, and plates)

Specifications

Industry Standard(s)	• IP69K in use • Listed to UL498 • Certified to CSA C22.2 No. 42 • Meets NEMA® WD-1, WD-6, and ANSI Standards • IP66 Suitability • NSF Certified (plugs, connectors and receptacles)
Nema Rating	L7-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	2-Pole



Current

Current/Amperage Rating	20 Amp
Description	
Amperage Rating	20 A
Voltage Rating Description	277 VAC
Voltage Rating	277 VAC

Dimensions

Width	3.10 in
Height	3.45 in
Length	4.56 in
Dimensions	4.56 in x 3.10 in x 3.45 in

General

Item Type	20A Watertight Single Receptacle
Type	Receptacle
UPC	781786379251
Color	Yellow

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)