



# Watertight Series, Locking Receptacle, 30A 250V, 2-Pole 3-Wire Grounding, NEMA L6-30R, Yellow

By Bryant  
Catalog # [BRY69W48](#)

Watertight Series, Locking Receptacle, 30A 250V, 2-Pole 3-Wire Grounding, NEMA L6-30R, Yellow

## Features

- Impact-resistant PBT material lid and cover plate
- Stainless steel mounting hardware
- Lockable cover meets OSHA Lockout/Tagout regulations
- Thermoplasticelastomer seal

## Performance

Moisture resistance: UL Listed to 3R, 3RX, 4, 4X, wet and damp locations (portable outlet boxes), UV resistance:All exposed materials are UV stabilized, Flammability:UL94V0 (boxes, covers, and plates)

## Specifications

|                      |                                                                                                                                                                                                                                                                              |
|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• IP69K in use</li><li>• Listed to UL498</li><li>• Certified to CSA C22.2 No. 42</li><li>• Meets NEMA® WD-1, WD-6, and ANSI Standards</li><li>• IP66 Suitability</li><li>• NSF Certified (plugs, connectors and receptacles)</li></ul> |
| Nema Rating          | L6-30P                                                                                                                                                                                                                                                                       |

## Conductor

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 3-Wire            |
| Wire Size       | #18 AWG to #8 AWG |
| Number Of Poles | 2-Pole            |



## Current

|                            |        |
|----------------------------|--------|
| Current/Amperage Rating    | 30 Amp |
| Description                |        |
| Amperage Rating            | 30 A   |
| Voltage Rating Description | 250 V  |
| Voltage Rating             | 250 V  |

## Dimensions

|            |                             |
|------------|-----------------------------|
| Width      | 3.10 in                     |
| Height     | 3.45 in                     |
| Length     | 4.56 in                     |
| Dimensions | 4.56 in x 3.10 in x 3.45 in |

## General

|           |                                  |
|-----------|----------------------------------|
| Item Type | 30A Watertight Single Receptacle |
| Type      | Receptacle                       |
| UPC       | 781786379343                     |
| Color     | Yellow                           |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)