



Surge Protective Devices, SPIKESHIELD
TVSS Plug Strips, 6) Receptacles, Metallic
Body, 1050 Joules, 6' Cord

By Bryant
Catalog # [BRY6MPS1050](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6)
Receptacles, Metallic Body, 1050 Joules, 6' Cord

Features

- 6) Receptacles
- Metallic Body
- 1050 Joules
- 6' Cord

Application

Standard Devices

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Cord Length	6 ft
-------------	------

Configuration

Number Of Outlets	6
-------------------	---

Current

Current Rating	15 A
Amperage Rating	15 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In



Voltage Rating	125 V
----------------	-------

Dimensions

Display Size	1050 Joules
--------------	-------------

General

Series	Economy Surge Strips
OEM Brand Name	Hubbell Bryant
Outlet	Straight Blade 5-15R
Color	Office White
Item Type	Surge Protection Plug Strips
Material - Mounting Hardware	Portable
Type	Metallic
Material	Steel
UPC	781786141582

Logistics

Carton Quantity	20
-----------------	----

Operational

Response Time	5
Indicator(s) Type	LED Indicator
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)