



Straight Blade Devices, Plug Strip, 6) Receptacles, Non-Metallic Body, 6' Cord

By Bryant
Catalog # [BRY6PPS](#)

Straight Blade Devices, Plug Strip, 6) Receptacles, Non-Metallic Body , 6' Cord



Features

- 6) Receptacles
- Non-Metallic Body
- 6' Cord

Application

6 Outlet, Heavy Duty Devices

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Cord Length	6 ft
-------------	------

Configuration

Number Of Outlets	6
-------------------	---

Current

Current Rating	15 A
Amperage Rating	15 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Plug-In

Voltage Rating	125 V
----------------	-------

Dimensions

Display Size	Standard
--------------	----------

General

Series	Economy Power Strips (no SPD)
OEM Brand Name	Hubbell Bryant
Outlet	Straight Blade 5-15R
Color	Office White
Item Type	Plug Strips
Material - Mounting Hardware	Portable
Type	Non-Metallic
Material	Non-Metallic
UPC	781786141605

Logistics

Carton Quantity	12
-----------------	----

Operational

Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
-----------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)



A Hubbell brand