



Surge Protective Devices, Plug Strip, 6 Receptacles, 350 Joule Rating, 15' Cord

By Bryant
Catalog # [BRY6PS35015](#)

Surge Protective Devices, Plug Strip, 6 Receptacles, 350 Joule Rating, 15' Cord



Features

- 6 Receptacles
- 350 Joule Rating
- 15' Cord

Application

Standard Devices

Specifications

EU RoHS Indicator No

Current

Amperage Rating 15 A
Frequency Rating 60 Hz
Phase Single Phase
Connectivity Plug-In
Voltage Rating 125 VAC

General

OEM Brand Name	Hubbell Bryant
Outlet	Straight Blade 5-15R
Material - Mounting Hardware	Portable
Material	Non-Metallic
UPC	781786141629

Logistics

Carton Quantity 12

Operational

Response Time	5
Indicator(s) Type	LED Indicator
Operating Temperature	34 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)