



Cord and Cable Reels, Commercial Cord Reel, 40' 15A 125V with Triple Tap, Yellow

By Bryant
Catalog # [BRYC40123TT](#)

Cord and Cable Reels, Commercial Cord Reel, 40' 15A 125V with Triple Tap, Yellow



Features

- 40' 15A 125V with Triple Tap
- Yellow

Application

Bench, Ceiling and Wall Mounted

Specifications

EU RoHS Indicator No

Conductor

Feeder Cord	12/3 SJTW
Cable Type	#16/3 SJT
Nema Color	Black
Cable Specification	12/3 SJTW

Configuration

Base Type Optional

Current

Duty Heavy Duty

Current / Amperage Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 VAC
Voltage Rating	125 VAC

Dimensions

Cable Length Active	480
Reel Frame Dimension	Steel
Cable Length Inactive	24
Cable Length	40 Ft.

General

Item Type	Reel with Triple Tap
Construction	Steel
Type	Reel With Triple Tap 15A 125V Connector
Series	Commercial
OEM Brand Name	Hubbell Bryant
UPC	781786128217

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)