



TECH-SPEC, Motor Disconnect Switch,
100A Non-Metallic Replacement Cover,
NEMA 4X,12

By Bryant
Catalog # [BRYDS100RC](#)

Replacement Cover for 30A Non-metallic BRYDS100 style disconnects

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Maintains IP67 and Type 4X water ingress protection when used with the BRYDS100 series
- Includes replacement gasket
- Captive Stainless Steel screws

Application

Indoor and Outdoor

Specifications

Industry Standard(s)	• cULus • UL60947-1 CSA C22.2, UL60947-4-1, UL50, UL50E, UL508, UL746C
Environmental Conditions	NEMA 4X, IP69K
Nema Rating	4X, 12



Dimensions

Size	9.9 in x 6.87 in
Width	6.87 in
Weight	3.1 lb.

General

Type	Accessories
Enclosure Type	Non-Metallic
Material	PBT
UPC	781786965744
Style	Replacement Cover
Mounting Type	Screw

Operational

Operating Temperature	• Maximum Continuous 75 °C • Minimum Continuous -40°C without impact
Action	Rotary