



TECH-SPEC, Motor Disconnect Switch, 3 Pole, 30A 600V AC, NEMA 4X,12 Non-Metallic Enclosure

By Bryant
Catalog # BRYDS30

TECH-SPEC, 30A Enclosed Motor Disconnect

Features

- UL 508 / UL 60947-4-1 HP rated motor disconnect
- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- IP67 and Type 4X Water Ingress protection
- Moveable mounting feet
- Stainless Steel captive screws
- Cover cannot be removed with switch in "on position"
- Replacement cover, switch and feet available

Application

Indoor and Outdoor

Specifications

Industry Standard(s)	• cULus • UL60947-1 CSA C22.2, UL60947-4-1, UL50, UL50E, UL508, UL746C
Environmental Conditions	NEMA 4X, IP69K
Nema Rating	4X, 12

Conductor

Number Of Poles	3
-----------------	---

Configuration

Mounting Method	External
Contact Configuration	Two Position

Current



Phase	3-Phase
Dielectric Strength	Withstands 3000V AC minimum
Contact Rating	30A
Amperage Rating	30 A
Wattage	18000 W
Voltage Rating	600 V

Dimensions

Size	7.6 in x 5.1 in x 4.1 in
Width	5.1 in
Weight	2.305 lb.

General

Type	Disconnect Switches
Enclosure Type	Non-Metallic
Material	PBT
UPC	781786965751
Style	Heavy Duty
Mounting Type	Moveable feet

Logistics

Carton Quantity	8
-----------------	---

Operational

Operating Cycles	Minimum 10,000
Operating Temperature	• Maximum Continuous 75 °C • Minimum Continuous -40°C without impact
Action	Rotary