



TECH-SPEC, Motor Disconnect Switch, 30A
Stainless Steel Replacement Cover, NEMA
4X,12

By Bryant
Catalog # [BRYDS30SSRC](#)

TECH-SPEC, 30A stainless steel Replacement cover

Features

- Formed in nonporous 304 stainless steel
- Type 4X,12K water ingress protection
- Highly visible yellow handle which meets OSHA Lockout/Tagout capabilities
- Cover cannot be removed with switch in "on position"

Application

Indoor and Outdoor

Specifications

Industry Standard(s)	• cULus • UL60947-1 CSA C22.2, UL60947-4-1, UL50, UL50E, UL508, UL746C
Environmental Conditions	NEMA 4X, IP69K
Nema Rating	4X, 12

Configuration

Contact Configuration	Two Position
-----------------------	--------------



Dimensions

Size	7 in x 4.9 in x 5.39
Width	4.9 in
Weight	1.9 lb.

General

Type	Accessories
Enclosure Type	Stainless Steel
Material	304 Stainless Steel
UPC	781786967038
Style	Replacement Cover
Mounting Type	Screw

Operational

Operating Cycles	Minimum 10,000
Operating Temperature	• Maximum Continuous 75 °C • Minimum Continuous -40°C without impact
Action	Rotary