



TECH-SPEC, Fused Disconnect Switch,
Fused, 3 Pole, 60A 600V AC, NEMA 4X,12
Non-Metallic Enclosure, for Use with Class
"J" fuses

By Bryant
Catalog # [BRYFD60](#)

TECH-SPEC, 60A fused disconnect

Features

- UL 98 HP rated fused disconnect
- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Lockable high visibility red handle for OSHA Lockout/Tagout
- Accepts class "J" fuses
- Type 4X, 12 water ingress
- Cover cannot be removed with switch in "on position"

Application

Indoor and Outdoor

Specifications

Industry Standard(s)	• cULus • UL 98
Environmental Conditions	NEMA 4X, IP69K
Nema Rating	4X, 12

Conductor

Number Of Poles	3
-----------------	---

Configuration

Mounting Method	External
Contact Configuration	Two Position

Current

Phase	3-Phase
-------	---------



Dielectric Strength

Withstands 3000V AC
minimum

Contact Rating
Amperage Rating
Wattage
Voltage Rating

60A
60 A
36000 W
600 V

Dimensions

Size
Weight

15. in x 11.46 in x 7.27
16.242 lb.

General

Type
Enclosure Type
Material
UPC
Style
Mounting Type

Fused Disconnect Switches
Non-Metallic
PBT
781786967182
Heavy Duty
External mounting feet

Logistics

Carton Quantity	2
-----------------	---

Operational

Operating Cycles
Operating Temperature

Minimum 10,000
• Maximum Continuous 75 °C
• Minimum Continuous -40°C
without impact

Action	Side
--------	------