



Temporary Lighting Products, 400W High Bay Light, 29, 000 Lumen Output

By Bryant
Catalog # [BRYMHHB400](#)

Temporary Lighting Products, 400W High Bay Light, 29,000 Lumen Output

Features

- 000 Lumen Output

Current

Current / Amperage Rating	15 A
Wattage	400 W
Voltage Rating	125 VAC

General



Type	Metal Halide
Series	High Bay Light
UPC	781786379947
Light Source	Metal Halide

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)