



Temporary Lighting Products, LED
Maintenance Light, 28W, 2928 Lumen
Output, 25' Cord

By Bryant
Catalog # [BRYML2825L](#)

Temporary Lighting Products, LED Maintenance Light, 28W, 2928
Lumen Output, 25' Cord

Features

- 28W
- 2928 Lumen Output
- 25' Cord

Conductor

Cord Length25 ft

Current

Wattage28 W

General



Type	LED
Series	Portable work Light
UPC	781786379862
Light Source	Fluorescent

Operational

Light Output2928 lm

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)