



Straight Blade Devices, Receptacles,
Duplex, Commercial Grade, 1/2 Controlled,
15A 125V, 2-Pole 3-Wire Grounding, 5- 15R,
Ivory

By Bryant
Catalog # [CBRS15C1I](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
1/2 Controlled, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Ivory



Features

- Duplex
- Commercial Grade
- 1/2 Controlled
- 15A 125V
- 2-Pole 3-Wire Grounding

Specifications

Nema Rating5-15R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating15 A
Current Rating15 A
Voltage Rating Description125 V
Voltage Rating125 V

Dimensions

Display SizeStandard Sized Product
Weight0.25 lb.

General

TypeDuplex Receptacle
SeriesCommercial
OEM Brand NameHubbell Bryant
UPC781786145900
StyleSmooth Face
ColorIvory

Logistics

Carton Quantity10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)