



Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, 15A 125V, 5-15R

By Bryant
Catalog # [CBRS15WWRTR](#)

Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, Back and Side Wired, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White



Features

- Commercial Grade
- Back and Side Wired
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Specifications

Nema Rating 5-15R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Voltage Rating Description 250 V
Current Rating 15 A
Voltage Rating 250 V
Connectivity Back and Side Wired

Current / Amperage Rating 15 A

Dimensions

Display Size Standard Sized Product
Weight 0.2 lb.

General

Color White
Style Smooth Face
Series Commercial
OEM Brand Name Hubbell Bryant
UPC 781786146723
Type Duplex Receptacle

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)