



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown, Single Pack

By Bryant
Catalog # [CBRS20](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Brown, Single Pack



Features

- Duplex
- Commercial Grade
- 20A 125V
- 2- Pole 3-Wire Grounding
- 5-20R

Application

Commercial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Back and Side Wired

Wattage	2500
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.38 in
Weight	0.2 lb.
Height	1.07 in
Dimensions	3.28 in x 1.38 in x 1.07 in

General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Style	Smooth Face
Color	Brown
Item Type	Traditional Duplex Smooth Face
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
Material	Composite
UPC	781786161153

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)