



Straight Blade Devices, Receptacles,
Duplex, Tamper-Resistant Commercial
Grade, 20A 125V, 2- Pole 3-Wire Grounding,
5-20R, Black, Single Pack

By Bryant
Catalog # [CBRS20BLKTR](#)

Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant
Commercial Grade, 20A 125V,2- Pole 3-Wire Grounding, 5-20R,
Black, Single Pack

Features

- Duplex
- Tamper-Resistant Commercial Grade
- 20A 125V
- 2- Pole 3-Wire Grounding
- 5-20R

Application

Commercial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase



Current / Amperage Rating	20 A
Connectivity	Back and Side Wired
Wattage	2500
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb.

General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Style	Smooth Face
Color	Black
Item Type	Traditional Duplex Smooth Face
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
Material	Composite
UPC	781786410695

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)