



Straight Blade Devices, Receptacles,
Duplex, Commercial Grade, Controlled, 20A
125V, 2-Pole 3-Wire Grounding, 5-20R,
Ivory

By Bryant
Catalog # [CBRS20C2I](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
Controlled, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

Features

- Duplex
- Commercial Grade
- Controlled
- 20A 125V
- 2-Pole 3-Wire Grounding

Specifications

Nema Rating5-20R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating20 A
Voltage Rating Description125 V
Voltage Rating125 V



Dimensions

Weight0.25 lb.

General

TypeDuplex Receptacle
SeriesCommercial
UPC781786146204
StyleSmooth Face
ColorIvory

Logistics

Carton Quantity10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)