



Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant Commercial Grade, 20A 125V, 2- Pole 3-Wire Grounding, 5-20R, Ivory, Single Pack

By Bryant
Catalog # [CBRS20ITR](#)

Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant Commercial Grade, 20A 125V,2- Pole 3-Wire Grounding, 5-20R, Ivory, Single Pack

Features

- Duplex
- Tamper-Resistant Commercial Grade
- 20A 125V
- 2- Pole 3-Wire Grounding
- 5-20R

Application

Commercial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	125 V
Current Rating	20 A
Voltage Rating	125 V



Wattage	2500
Connectivity	Back and Side Wired
Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb.

General

Color	Ivory
Style	Smooth Face
Series	Commercial
OEM Brand Name	Hubbell Bryant
UPC	781786410718
Type	Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Traditional Duplex Smooth Face
Material	Composite

Logistics

Pallet Quantity	8500
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)