



Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, 20A 125V, 5-20R

By Bryant
Catalog # [CBRS20LAWRTR](#)

Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, Back and Side Wired, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Light Almond



Features

- Commercial Grade
- Back and Side Wired
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Specifications

Nema Rating 5-20R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Current / Amperage Rating 20 A
Voltage Rating Description 125 V

Voltage Rating 125 V

Dimensions

Weight 0.2 lb.

General

Type Duplex Receptacle
Series Commercial
UPC 781786146785
Style Smooth Face
Color Light Almond

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)