



# Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, 20A 125V, 5-20R

By Bryant  
Catalog # [CBRS20WRTR](#)

Straight Blade Devices, Tamper and Weather Resistant Duplex Receptacle, Commercial Grade, Back and Side Wired, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown



### Features

- Commercial Grade
- Back and Side Wired
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

### Specifications

Nema Rating 5-20R

### Conductor

Number Of Poles 2-Pole  
Number Of Wires 3-Wire

### Current

Voltage Rating 125 V  
Voltage Rating Description 125 V

Current / Amperage Rating 20 A

### Dimensions

Weight 0.2 lb.

### General

Color Brown  
Style Smooth Face  
UPC 781786146754  
Type Duplex Receptacle  
Series Commercial

### Logistics

Carton Quantity 10

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)