



# Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray, Single Pack, Isolated Ground

By Bryant  
Catalog # [CR20IGRY](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray, Single Pack, Isolated Ground



## Features

- Duplex
- Commercial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

## Application

Commercial Specification Grade

## Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

## Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

## Current

Current Rating	20 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	20 A
Connectivity	Back and Side Wired
Wattage	1875

Voltage Rating 125 V

## Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	1.38 in
Weight	0.2 lb.
Height	0.92 in
Dimensions	3.28 in x 1.38 in x 0.92 in

## General

Series	Straight Blade
OEM Brand Name	Hubbell Bryant
Style	Smooth Face
Color	Gray
Item Type	Traditional Duplex Smooth Face
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
Material	Composite
UPC	781786734746

## Logistics

Carton Quantity	10
Pallet Quantity	5500

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)