



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, Single Pack, Isolated Ground

By Bryant
Catalog # [CR20IGW](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White, Single Pack, Isolated Ground



Features

- Duplex
- Commercial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Application

Commercial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Current Rating	20 A
Voltage Rating	125 V
Wattage	1875
Connectivity	Back and Side Wired
Phase	Single Phase

Current / Amperage Rating20 A

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Weight	0.2 lb.
Height	0.92 in
Width	1.38 in
Dimensions	3.28 in x 1.38 in x 0.92 in

General

Color	White
Style	Smooth Face
Series	Straight Blade
OEM Brand Name	Hubbell Bryant
UPC	781786734760
Type	Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Traditional Duplex Smooth Face
Material	Composite

Logistics

Pallet Quantity	5500
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)