



Straight Blade Devices, Receptacles,
Duplex, Commercial Grade, 15A 125V, 2-
Pole 3-Wire Grounding, 5-15R, Black, Single
Pack

By Bryant
Catalog # [CRS15BLK](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Black, Single Pack

Features

- Duplex
- Commercial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Application

Commercial Specification Grade

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Current Rating	15 A
Voltage Rating	125 V
Wattage	1875



Connectivity	Side Wired Only
Phase	Single Phase
Current / Amperage Rating	15 A
Dimensions	
Length	3.28 in
Display Size	Standard Sized Product
Weight	0.2 lb.
Height	1.07 in
Width	1.38 in
Dimensions	3.28 in x 1.38 in x 1.07 in
General	
Color	Black
Style	Smooth Face
Series	Commercial
OEM Brand Name	Hubbell Bryant
UPC	781786161030
Type	Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Traditional Duplex Smooth Face
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)