



Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Light Almond, Single Pack

By Bryant
Catalog # [CRS15LATR](#)

Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Light Almond, Single Pack

Features

- Duplex
- Tamper-Resistant Commercial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5- 15R

Application

Commercial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Phase	Single Phase



Current / Amperage Rating	15 A
Connectivity	Side Wired Only
Wattage	1875
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Weight	0.15 lb.

General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Style	Smooth Face
Color	Light Almond
Item Type	Traditional Duplex Smooth Face
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
Material	Composite
UPC	781786144002

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)