



Straight Blade Devices, Receptacles,
Duplex, Commercial Grade, 20A 125V, 2-
Pole 3-Wire Grounding, 5-20R, Gray, Single
Pack

By Bryant
Catalog # [CRS20GRY](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade,
20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray, Single Pack

Features

- Duplex
- Commercial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Application

Commercial Specification Grade

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	125 V
Current Rating	20 A
Voltage Rating	125 V
Wattage	2500



Connectivity	Side Wired Only
Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Weight	0.2 lb.
Height	1.07 in
Width	1.38 in
Dimensions	3.28 in x 1.38 in x 1.07 in

General

Color	Gray
Style	Smooth Face
Series	Commercial
OEM Brand Name	Hubbell Bryant
UPC	781786161061
Type	Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Traditional Duplex Smooth Face
Material	Composite

Logistics

Pallet Quantity	9000
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)