

BRYA

**Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V,
2-Pole 3-Wire Grounding, 5-20R, Ivory, Single Pack**

By Bryant

Catalog # [CRS20I](#)

Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory, Single Pack



Features

- Duplex
- Commercial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

Application

Commercial Specification Grade

Specifications

Standards - RoHS Compliance Status
CM
Environmental Conditions
Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator
Yes
Nema Rating
5-20R

Conductor

Number Of Wires
3-Wire
Wire Size
#14 AWG to #12 AWG
Number Of Poles
2-Pole

Current

Amperage Rating
20 A
Voltage Rating Description
125 V
Current Rating
20 A
Voltage Rating
125 V
Wattage
2500
Connectivity
Side Wired Only
Phase
Single Phase
Current / Amperage Rating
20 A

Dimensions

Length
3.28 in
Display Size
Standard Sized Product
Weight
0.2 lb.
Height
1.07 in
Width
1.38 in
Dimensions
3.28 in x 1.38 in x 1.07 in

General

Color
Ivory
Style
Smooth Face
Series
Commercial
UPC
781786161078
Type
Duplex Receptacle
Material - Mounting Hardware
Screw Mounting
Item Type
Traditional Duplex Smooth Face
Material
Composite

Logistics

Pallet Quantity
9000
Carton Quantity

Product Assets

[Catalog \[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRY_CA-CRS20I-SPEC-EN | REV 5/2026