



Locking Devices, Industrial, Receptacle,
50A 125/250, 3-Pole 4-Wire Grounding,
Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS6369A](#)

Twist-Lock® Industrial Receptacle 50A

Features

- Thermoset construction offers high heat resistance
- Armored housing provides superior impact resistance
- One piece contacts provide low operating temperatures

Application

Extra Heavy Duty Industrial Specification Grade

Specifications


Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Industry Standard(s)	WR Rating

Conductor

Number Of Wires	4-Wire
Wire Size	#10 AWG to #4 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	125/250V AC
Phase	Single Phase
Connectivity	Pressure Terminal Screws



Voltage Rating	125/250 VAC
----------------	-------------

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	2.12 in
Height	2.44 in
Dimensions	3.28 in x 2.12 in x 2.44 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	50A Single Armored Nylon Receptacle
Material - Mounting Hardware	Screw Mounting Receptacle
Type	Receptacle
Material	Composite
UPC	781786253094

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)