



Locking Devices, Twist-Lock®, Economy, Flanged Inlet, 50A 125/250, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel

By Bryant
Catalog # [CS6375LC](#)

Locking Devices, Twist-Lock®, Economy, Flanged Inlet, 50A 125/250, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Steel

Features

- Metallic flanged casing provides maximum strength and protection
- Thermoset interior provides superior heat resistance

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A



Amperage Rating	50 A
Voltage Rating Description	125/250V AC
Phase	Single Phase
Connectivity	Pressure Terminal Screws
Voltage Rating	125/250 VAC

Dimensions

Display Size	Standard Sized Product
Length	2.70 in

General

Style	Heavy Duty
Color	Metallic
Item Type	50A Male Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Thermoplastic
UPC	783585320724

Logistics

Carton Quantity	30
Pallet Quantity	1620

Product Assets

[Catalog \[English\]](#)