



Locking Devices, Industrial, Male Plug, 50A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Bryant
Catalog # CS8265

Locking Devices, Industrial, Male Plug, 50A 250V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Features

- Super tough nylon housing offers better impact qualities
- Stainless steel shroud protects contacts and prevents mismating
- Box terminal with hex socket threaded slug, permits high clamping pressure on conductors without damaging strands
- Thermoplastic polyester interior provides heat resistance and impact strength

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Industry Standard(s)	• Listed to UL498 • Certified to CSA, C22.2, No. 42

Conductor

Number Of Wires	3-Wire
Wire Size	#10 AWG to #6 AWG
Number Of Poles	2-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	50 Amp
Description	



Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	250 VAC
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	250 VAC

Dimensions

Display Size	Standard Sized
Length	6.38 in
Width	2.56 in
Height	2.56 in
Dimensions	6.38 in x 2.56 in x 2.56 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	50A Heavy Duty Male Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786831148

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)