



Locking Devices, Industrial, Male Plug, 50A 3- PhaseDelta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Bryant
Catalog # [CS8365](#)

Locking Devices, Industrial, Male Plug, 50A 3- PhaseDelta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Features

- Super tough nylon housing offers better impact qualities
- Stainless steel shroud protects contacts and prevents mismatching
- Box terminal with hex socket threaded slug, permits high clamping pressure on conductors without damaging strands
- Thermoplastic polyester interior provides heat resistance and impact strength

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current

Current/Amperage Rating	50 Amp
Description	



Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	3 Phase 250 VAC
Phase	Three Phase
Connectivity	Screw Terminals
Voltage Rating	3 Phase 250 VAC

Dimensions

Display Size	Standard Sized
Length	6.38 in
Width	2.56 in
Height	2.56 in
Dimensions	6.38 in x 2.56 in x 2.56 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	50A Heavy Duty Male Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786538177

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)