



Locking Devices, Locking Devices,
Industrial, Receptacle, 50A 3-Phase Delta
250V AC, 3-Pole 4-Wire Grounding, Non-
NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS8369A](#)

Locking Devices, Locking Devices, Industrial, Receptacle, 50A 3-
Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA,
Screw Terminal, Black



Features

- Thermoset construction offers high heat resistance
- Armored housing provides superior impact resistance
- One piece contacts provide low operating temperatures

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Industry Standard(s)	WR Rating

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	3-Pole

Current

Current/Amperage Rating	50 Amp
Description	
Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	3 Phase 250V AC
Phase	Three Phase
Connectivity	Pressure Terminal Screws

Voltage Rating	3 Phase 250 VAC
----------------	-----------------

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Width	2.12 in
Height	2.44 in
Dimensions	3.28 in x 2.12 in x 2.44 in

General

OEM Brand Name	Hubbell Bryant
Style	Extra Heavy Duty
Color	Black
Item Type	50A Single Armored Heavy Duty Receptacle
Material - Mounting Hardware	Screw Mounting Receptacle
Type	Receptacle
Material	Composite
UPC	781786253179

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)