



Locking Devices, Twist-Lock®, Economy, Flanged Inlet, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS8375L](#)

Locking Devices, Twist-Lock®, Economy, Flanged Inlet, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non- NEMA, Screw Terminal, Black

Features

- Metallic flanged casing provides maximum strength and protection
- Thermoset interior provides superior heat resistance

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Phase	Three Phase
Current/Amperage Rating	50 Amp
Description	
Connectivity	Pressure Terminal Screws



Current Rating	50 A
Amperage Rating	50 A
Voltage Rating Description	3 Phase 250V AC
Voltage Rating	3 Phase 250 VAC

Dimensions

Display Size	Standard Sized Product
Length	2.70 in

General

Item Type	50A Male Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Type	Flanged Inlet
Material	Thermoplastic
UPC	783585320762
Style	Heavy Duty
Color	Metallic

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalog \[English\]](#)