



Deluxe Cord Grip, 90 Degree Male, .312-.375", 3/8" With Mesh

By Bryant
Catalog # [DC31938](#)

Deluxe Cord Grip, 90 Degree Male, .312-.375", 3/8" With Mesh

Features

- .312-.375"
- 3/8" With Mesh

Application

90 Degree Male

General

Catalog Number	DC31938
EU RoHS Indicator	No
Material	Aluminum Fitting, Stainless Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Deluxe Cord Grips
Style	For Insulated Cables



Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Thread Size	3/8 NPT
Type	90 Degree Male Thread
UPC	781786243620

Conductor Related

Cable Diameter Range	0.312 in-0.375 in
Number of Conductors	Jacketed UL Listed Cable Only

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - DC31938 Specification Sheet French](#)
[Specifications - DC31938 Specification Sheet English](#)