



Straight Blade Devices, Receptacles,
Decorator Duplex, Commercial Grade,
Controlled, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Ivory

By Bryant
Catalog # [DRS15C2I](#)

Straight Blade Devices, Receptacles, Decorator Duplex,
Commercial Grade, Controlled, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Ivory

Features

- Decorator Duplex
- Commercial Grade
- Controlled
- 15A 125V
- 2-Pole 3-Wire Grounding

Specifications

Nema Rating5-15R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating15 A
Amperage Rating15 A
Voltage Rating Description125 V
Voltage Rating125 V



Dimensions

Weight0.25 lb.

General

Item TypeDecorator Duplex
TypeDuplex Receptacle
SeriesCommercial
OEM Brand NameHubbell Bryant
UPC781786146082
StyleDecorator
ColorIvory

Logistics

Carton Quantity10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)