



Straight Blade Devices, Tamper and Weather Resistant, Decorator Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray

By Bryant
Catalog # [DRS15GRYWRTTR](#)

Straight Blade Devices, Tamper and Weather Resistant, Decorator Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray

Features

- Duplex
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R
- Gray

Specifications

Nema Rating5-15R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Amperage Rating15 A
Voltage Rating Description125 V
Current / Amperage Rating15 A
ConnectivityBack and Side Wired



Voltage Rating125 V

Dimensions

Weight0.2 lb.

General

SeriesCommercial
OEM Brand NameHubbell Bryant
StyleDecorator
ColorGray
Item TypeDecorator Duplex
TypeDuplex Receptacle
UPC781786146839

Logistics

Carton Quantity10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)