



Straight Blade Devices, Tamper and Weather Resistant, Decorator Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond

By Bryant
Catalog # [DRS15LAWRTR](#)

Straight Blade Devices, Tamper and Weather Resistant, Decorator Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond

Features

- Duplex
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R
- Light Almond

Specifications

Nema Rating5-15R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating15 A
ConnectivityBack and Side Wired
Amperage Rating15 A
Voltage Rating Description125 V



Voltage Rating125 V

Dimensions

Weight0.2 lb.

General

Item TypeDecorator Duplex
TypeDuplex Receptacle
SeriesCommercial
OEM Brand NameHubbell Bryant
UPC781786146853
StyleDecorator
ColorLight Almond

Logistics

Carton Quantity10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)