



Straight Blade Devices, Receptacles,
Duplex, Decorator, Commercial/Industrial
Grade, 15A 125V, 2-Pole 3-Wire Grounding,
5-15R, White, Single Pack

By Bryant
Catalog # [DRS15WHI](#)

Straight Blade Devices, Receptacles, Duplex, Decorator,
Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire Grounding,
5-15R, White, Single Pack



Features

- Duplex
- Decorator
- Commercial/Industrial Grade
- 15A 125V
- 2-Pole 3-Wire Grounding

Application

Commercial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 V
Current Rating	15 A
Voltage Rating	125 V
Wattage	1875
Connectivity	Back and Side Wired Terminal Screws

Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Weight	0.15 lb.
Height	1.07 in
Width	1.38 in
Dimensions	3.28 in x 1.38 in x 1.07 in

General

Color	White
Style	Decorator
Series	Commercial
OEM Brand Name	Hubbell Bryant
UPC	781786410503
Type	Duplex Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	Decorator Duplex
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)