



Straight Blade Devices, Receptacles,
Tamper- Resistant Duplex, Decorator,
Commercial/Industrial Grade, 20A 125V, 2-
Pole 3-Wire Grounding, 5-20R

By Bryant
Catalog # [DRS20LATR](#)

Straight Blade Devices, Receptacles, Tamper- Resistant Duplex,
Decorator, Commercial/Industrial Grade, 20A 125V, 2- Pole 3-
Wire Grounding, 5-20R, Light Almond, Single Pack

Features

- Tamper- Resistant Duplex
- Decorator
- Commercial/Industrial Grade
- 20A 125V
- 2- Pole 3-Wire Grounding

Application

Commercial Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Current Rating	20 A
Amperage Rating	20 A
Voltage Rating Description	125 V
Phase	Single Phase



Current / Amperage Rating	20 A
Connectivity	Back and Side Wired Terminal Screws
Wattage	2500
Voltage Rating	125 V

Dimensions

Display Size	Standard Sized Product
Weight	0.15 lb.

General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Style	Decorator
Color	Light Almond
Item Type	Decorator Duplex
Material - Mounting Hardware	Screw Mounting
Type	Duplex Receptacle
Material	Composite
UPC	781786144217

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)