



Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1"

By Bryant
Catalog # [FC100](#)

Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1"



Features

- Straight Male
- 1"

Application

Straight Male

Specifications

EU RoHS Indicator	No
Nema Rating	Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Current

Connectivity	Cap Nut
--------------	---------

Dimensions

Conduit Trade Size	1 in
--------------------	------

General

Series	Liquidtight Conduit
OEM Brand Name	Hubbell Bryant
Style	For Metal & Non-Metallic PolyTuff I
Material - Mounting Hardware	Between Enclosure and Conduit
Type	Straight With Male Fitting
Material	Steel Fitting, Stainless Steel Mesh
UPC	781786241060

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)