



## Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1 1/4"

By Bryant  
Catalog # [FC125](#)

Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1 1/4"



### Features

- Straight Male
- 1 1/4"

### Application

Straight Male

### Specifications

EU RoHS Indicator	No
Nema Rating	Suitable for use in hazardous locations per Class I Div 2, Class II Div 1 & 2, Class III Div 1 & 2

### Current

Connectivity	Cap Nut
--------------	---------

### Dimensions

Conduit Trade Size	1 1/4 in
--------------------	----------

### General

Material - Mounting Hardware	Between Enclosure and Conduit
Type	Straight With Male Fitting
Series	Liquidtight Conduit
OEM Brand Name	Hubbell Bryant
Material	Steel Fitting, Stainless Steel Mesh
UPC	781786241084
Style	For Metal & Non-Metallic PolyTuff I

### Logistics

Carton Quantity	2
-----------------	---

### Operational

Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
--------------------	---

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)