



Liquid-Tight Flexible Metallic Conduit Grip, Connector, 90 Degree Male, 1 1/4"

By Bryant
Catalog # [FC12590](#)

Liquid-Tight Flexible Metallic Conduit Grip, Connector, 90 Degree Male, 1 1/4"



Features

- 90 Degree Male
- 1 1/4"

Application

90 Degree Male

Specifications

EU RoHS Indicator	No
Nema Rating	Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Current

Connectivity	Cap Nut
--------------	---------

Dimensions

Conduit Trade Size	1 1/4 in
--------------------	----------

General

Series	Liquidtight Conduit
OEM Brand Name	Hubbell Bryant
Style	For Metal & Non-Metallic PolyTuff I
Material - Mounting Hardware	Between Enclosure and Conduit
Type	90 Degree With Male Fitting
Material	Steel Fitting, Stainless Steel Mesh
UPC	781786241282

Logistics

Carton Quantity	2
-----------------	---

Operational

Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)