



Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1/2"

By Bryant
Catalog # [FC50](#)

Liquid-Tight Flexible Metallic Conduit Grip, Connector, Straight Male, 1/2"

Features

- Straight Male
- 1/2"

Application

Straight Male

Specifications

EU RoHS Indicator	No
Nema Rating	Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Current

Connectivity	Cap Nut
--------------	---------

Dimensions

Conduit Trade Size	1/2 in
--------------------	--------

General



Series	Liquidtight Conduit
OEM Brand Name	Hubbell Bryant
Style	For Metal & Non-Metallic PolyTuff I
Material - Mounting Hardware	Between Enclosure and Conduit
Type	Straight With Male Fitting
Material	Steel Fitting, Stainless Steel Mesh
UPC	781786241022

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
--------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)