



Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 3/4"

By Bryant
Catalog # [FC7545](#)

Liquid-Tight Flexible Metallic Conduit Grip, Connector, 45 Degree Male, 3/4"



Features

- 45 Degree Male
- 3/4"

Application

45 Degree Male

Specifications

EU RoHS Indicator	No
Nema Rating	Suitable for use in hazardous locations per Class 1 Div 2, Class II Div 1 & 2, Class III Div 1 & 2

Current

Connectivity	Cap Nut
--------------	---------

Dimensions

Conduit Trade Size	3/4 in
--------------------	--------

General

Material - Mounting Hardware	Between Enclosure and Conduit
Type	45 Degree With Male Fitting
Series	Liquidtight Conduit
OEM Brand Name	Hubbell Bryant
Material	Steel Fitting, Stainless Steel Mesh
UPC	781786241442
Style	For Metal & Non-Metallic PolyTuff I

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	-40 Deg F to 225 Deg F (-40 Deg C to 107 Deg C)
--------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)