



Lampholders, Fluorescent Starter, 14-15-20W

By Bryant
Catalog # [FS2A](#)

Lampholders, Fluorescent Starter, 14-15-20W



Features

- 14-15-20W

Application

Low Wattage Fluorescent

Specifications

EU RoHS Indicator No

Current

Frequency Rating 60 Hz
Wattage 14, 15, 20W
Voltage Rating 120/277V AC kV

General

Item Type Fluorescent Starters
Material - Mounting Hardware Plug-In

Type Neostart
Series Fluorescent Starters
OEM Brand Name Hubbell Bryant
Lamp Type Pre-Heat
UPC 781786689701
Color White

Logistics

Carton Quantity 25

Operational

Minimum Starting Temperature 40 Degrees F °
Start Type Neo-Start

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)