



Lampholders, Fluorescent Starter, 4-6-8W

By Bryant
Catalog # [FS5A](#)

Lampholders, Fluorescent Starter, 4-6-8W



Features

- 4-6-8W

Application

Low Wattage Fluorescent

Specifications

EU RoHS Indicator No

Current

Frequency Rating 60 Hz
Wattage 4, 6, 8W
Voltage Rating 120/277V AC kV

General

Item Type Fluorescent Starters
Material - Mounting Hardware Plug-In

Type Neostart
Series Fluorescent Starters
OEM Brand Name Hubbell Bryant
Lamp Type Pre-Heat
UPC 781786687943
Color White

Logistics

Carton Quantity 25

Operational

Minimum Starting Temperature 40 Degrees F °
Start Type Neo-Start

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)