



Locking Devices, Industrial, Female
Connector Body 30A 120V AC 400Hz, 2-
Pole 3-Wire Grounding, FSL2R, Screw
Terminal, Black and White

By Bryant
Catalog # [FSL2NC](#)

Locking Devices, Industrial, Female Connector Body 30A 120V
AC 400Hz, 2-Pole 3-Wire Grounding, FSL2R, Screw Terminal,
Black and White

Features

- Face and body feature alignment keys for easy assembly
- Amperage, voltage and NEMA configuration imprinted on face for easy identification
- Impact/chemical resistant, toughened nylon construction
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention
- Designed, tested and approved for use on 400 Hz (400 cycles per second) circuits

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	FSL2-R

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Conductors	3-Wire Grounding
Conductor Range	#12 AWG to #8 AWG
Number Of Poles	2-Pole

Current

Current/Amperage Rating	30 Amp 400 Hz
Description	
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	120 V
Connectivity	Screw Terminals



Voltage Rating	120 V
----------------	-------

Dimensions

Display Size	Standard Sized Product
Length	2.13 in
Width	2.13 in
Height	3.90 in
Dimensions	2.13 in x 2.13 in x 3.90 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	30A Triple Gripper Nylon Connector
Insulation	Insulated Body
Material - Mounting Hardware	Cord Mounted
Type	Connector Body
Material	Composite
UPC	781786638266

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)