



Locking Devices, Industrial, Male Plug, 30A 120V 400Hz, 2-Pole 3-Wire Grounding, FSL2P, Screw Terminal, Black and White

By Bryant
Catalog # [FSL2NP](#)

Locking Devices, Industrial, Male Plug, 30A 120V 400Hz, 2-Pole 3-Wire Grounding, FSL2P, Screw Terminal, Black and White

Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention
- Designed, tested and approved for use on 400 Hz (400 cycles per second) circuits

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	FSL2-P

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	2-Pole

Configuration

Cord Type	All Listed Portables
-----------	----------------------

Current



Current/Amperage Rating Description	30 Amp 400 Hz
Current Rating	30 A
Amperage Rating	30 A
Voltage Rating Description	120 V
Phase	Single Phase
Connectivity	Screw Terminals
Voltage Rating	120 V

Dimensions

Display Size	Standard Sized
Length	2.13 in
Width	2.13 in
Height	2.86 in
Dimensions	2.13 in x 2.13 in x 2.86 in

General

OEM Brand Name	Hubbell Bryant
Style	Internal Cord Clamp
Color	Black, White
Item Type	30A Triple Gripper Nylon Plug
Material - Mounting Hardware	Cord Mounted
Type	Plugs
Material	Composite
UPC	781786638273

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)



A Hubbell brand