




Fiber Optic Panel Adapter, 8 Fiber, 8) SC MTJR, Unloaded

By Bryant
Catalog # [FSPSC8X](#)

Fiber Optic Panel Adapter, 8 Fiber, 8) SC MTJR, Unloaded



Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

Specifications

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS
EU RoHS Indicator	Yes

Conductor

Fiber Size	125 Micron
------------	------------

Configuration

Number Of Ports	8
-----------------	---

Current

Connectivity	Receptacle
Return Loss	26
Insertion Loss	0.30 dB

General

Sub Brand	OptiChannel
Material - Mounting Hardware	Snap-In
Material	Ceramic Zirconium
Specifications	• Dimensions - 1.1" W X 5.1" H • Finish - Durable black powder coat • Material - 16ga cold rolled steel
UPC	662620218397
Color	Black

Logistics

Carton Quantity	4
-----------------	---

Operational

Service Life	500 matings
Adapter Type	SC Simplex/LC Duplex
Temperature Rating	-40C to +85C
Repeatability	0.1 dB

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)