



Wire Management Products, Special Purpose Splicing Grip, Flexible Tube, 24" Mesh Length, Steel, 0.50-0.61"

By Bryant
Catalog # [FTD05024](#)

Wire Management Products, Special Purpose Splicing Grip,
Flexible Tube, 24" Mesh Length, Steel, 0.50-0.61"



Features

- Flexible Tube
- 24" Mesh Length
- Steel
- 0.50-0.61"

Application

Cable and Wire Splicing

Specifications

EU RoHS Indicator No

Conductor

Number Of Conductors 1
Cable Diameter Range 0.5 in-0.61 in

Force Related

Approx Breaking Strength 3,200 lb.

General

Material - Mounting Hardware On Cable Ends
Type Tube
Series Splicing Grips
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786241640
Style Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)